Timing/Delay Modules Miniature Manual Variable Optical Delay Line – VariDelay™ I



Charlingtions

The VDL-002 is a miniaturized variable optical delay line designed specifically for OEM applications. With a delay range of up to 250 ps, this device is a superior replacement for the variable RF phase shifters inadequately adapted from the RF/wireless field for fiber optic communications. It is especially useful in coherent detection systems for adjusting phase or delay differences between signals. The VDL-002 eliminates the VSWR problems of RF phase shifters for high frequency and broadband signals, especially at 40 and 100Gbps. A single device can be used for any data rate, simplifying inventory management. With a footprint of only 0.72" x 1.46" x 2.2" for a delay range of 100 ps, the device can be conveniently integrated into network modules, test instruments, and OCT equipment for precision optical path length control or timing alignment. An internal mirror can be installed to cause light to double pass the device, doubling the delay range. The patent-pending design makes hermetically sealed packaging possible and enables Telcordia qualification when required. Finally, a locking mechanism is provided for locking the delay at a

permanent position. The VDL-002 generally comes with single mode or PM fiber pigtails per customer requirement.

Specifications:	
Operating Wavelength	SM: 1260 to 1650 nm PM: 1310 or 1550 ± 50nm Other wavelengths may be available upon request
Optical Delay Range	0 - 100 ps (3 cm) continuous for 100 ps model 0 - 250 ps (7.5 cm) continuous for 250 ps model Internal mirror option for doubling the range
Delay Stability	0.15 ps
Zero Point Delay Offset ¹	180 ps
Insertion Loss	1.0 dB nominal
Insertion Loss Variation	±0.3 dB over entire range
PDL	0.1 dB
Return Loss	55 dB
Extinction Ratio	> 18 dB for PM model
Optical Damage Power Threshold	300 mW
Operating Temperature	-15 to 50°C
Storage Temperature	-40 to 60°C
Fiber Type	SMF-28 or PM Panda fiber
Position Locking	Included
Dimensions	2.20" (L) \times 1.46" (W) \times 0.72" (H) for 100 ps model 3.15" (L) \times 1.46" (W) \times 0.72" (H) for 250 ps model

Features:

- \cdot Compact size
- · High resolution
- · Low insertion loss
- · High stability
- · Longevity

Applications:

- · Coherent detection systems
- \cdot Optical time division
- multiplexing (OTDM)
- Optical coherence tomography (OCT)
- Optical interferometry
- Optical Interferometry
 Optical Fourier spectrum
 analysis
- · Fiber sensors

lech Info: p. 223

Note: Values are referenced without connectors.

1. Absolute delay at 0 ps setting measured to the edge of the enclosure (excluding caps, boots, and pigtails).

2. Specifications in table apply for a single-pass device without connectors, measured over 1310 ± 50 nm or 1550 ± 50 nm. The output pigtail can also be replaced with a Faraday mirror to create a double pass device with a total range of 200 or 500 ps, respectively. Some specifications will change for this case. Contact General Photonics for details

Dimensions (in inches):

