KTP - Potassium Titanyl Phosphate (KTiOPO₄)

Introduction

Potassium Titanyl Phosphate (KTiOPO₄ or KTP) is widely used in both commercial and military lasers including laboratory and medical system, range-finders, LiDAR, optical communication and industrial systems.

CASTECH's KTP is featured by

- · Large nonlinear optical coefficient
- · Wide angular bandwidth and small walk-off angle
- · Broad temperature and spectral bandwidth
- · High electro-optic coefficient and low dielectric constant
- · Large figure of merit
- · Nonhydroscopic, chemically and mechanically stable.

CASTECH offers

- · Strict quality control
- Large crystal size up to $20 \times 20 \times 40$ mm³ and maximum length of 60 mm
- Quick delivery (15 working days for polished only, 20 working days for coated)
- · Unbeatable price and quantity discount
- · Technical support
- · AR-coating, mounting and re-working service

Basic Properties

Table 1. Chemical and Structural Properties

Crystal Structure	Orthorhombic, Space group Pna2 ₁ , Point group mm2
Lattice Parameter	a = 6.404 Å, b = 10.616 Å, c = 12.814 Å, Z = 8
Melting Point	About 1172 °C
Mohs Hardness	5
Density	3.01 g/cm ³
Thermal Conductivity	13 W/m/K
Thermal Expansion Coefficients	$\alpha_{\rm x} = 11 \times 10^{-6} / {\rm ^{\circ}C}, \alpha_{\rm y} = 9 \times 10^{-6} / {\rm ^{\circ}C}, \alpha_{\rm z} = 0.6 \times 10^{-6} / {\rm ^{\circ}C}$




Transparency Range		350-4500 nm
SHG Phase Matchable Range		497-1800 nm (Type II)
Therm-optic Coefficient (λ in μ m)		$dn_x/dT = 1.1 \times 10^{-5}$ /°C $dn_y/dT = 1.3 \times 10^{-5}$ /°C $dn_z/dT = 1.6 \times 10^{-5}$ /°C
Absorption Coefficients		<0.1% /cm at 1064 nm, <1% /cm at 532 nm
For Type II SHG of a Nd:YAG laser at 1064 nm	Temperature Acceptance	24 °C·cm
	Spectral Acceptance	0.56 nm·cm
	Angular Acceptance	14.2 mrad·cm (Φ); 55.3mrad·cm (θ)
	Walk-off Angle	0.55 °
NLO Coefficients		$d_{\rm eff}(II)\approx (d_{24}$ - $d_{15})$ $sin2\Phi$ $sin2\theta$ - $(d_{15}$ $sin^2\Phi+d_{24}$ $cos^2\Phi)$ $sin\theta$
Non-vanished NLO Susceptibilities		$d_{31} = 6.5 \text{ pm/V}$ $d_{24} = 7.6 \text{ pm/V}$ $d_{32} = 5 \text{ pm/V}$ $d_{15} = 6.1 \text{ pm/V}$ $d_{33} = 13.7 \text{ pm/V}$
Sellmeier Equations (λ in μ m)		$\begin{array}{l} n_x^2 = 3.0065 + 0.03901 / (\lambda^2 - 0.04251) - 0.01327 \lambda^2 \\ n_y^2 = 3.0333 + 0.04154 / (\lambda^2 - 0.04547) - 0.01408 \lambda^2 \\ n_z^2 = 3.3134 + 0.05694 / (\lambda^2 - 0.05658) - 0.01682 \lambda^2 \end{array}$
Electro-optic Coefficients:		Low frequency (pm/V) High frequency (pm/V)
r ₁₃		9.5 8.8
r ₂₃		15.7 13.8
r ₃₃		36.3 7.3 35.0 6.9
r ₅₁ r ₄₂		9.3 8.8
Dielectric Constant		$\varepsilon_{\text{eff}} = 13$


Applications for SHG and SFG of Nd: Lasers

KTP is the most commonly used material for frequency doubling of Nd: YAG and other Nd-doped lasers, particularly when the power density is at a low or medium level. Up to now, Nd: lasers that use KTP for intra-cavity and extra-cavity frequency doubling have become a preferred pumping sources for visible dye lasers and tunable Ti:sapphire lasers as well as their amplifiers. They are also used as green sources for many research and industry applications.

- Close to 80% conversion efficiency and 700 mJ green laser were obtained with a 900 mJ injection-seeded Q-switch Nd:YAG lasers by using extra-cavity KTP.
- 8 W green laser was generated from a 15 W LD pumped Nd:YVO₄ with intra-cavity KTP.

KTP is also being used for intracavity mixing of 0.81 μm diode and 1.064 μm Nd:YAG laser to generate blue light and intracavity SHG of Nd:YAG or Nd:YAP lasers at 1.3 μm to produce red light.






Applications for OPG, OPA and OPO

As an efficient OPO crystal pumped by a Nd:laser and its second harmonics, KTP plays an important role for parametric sources for tunable outputs from visible (600 nm) to mid-IR (4500 nm), as shown in Fig. 3 and Fig. 4.

Generally, KTP's OPOs provide stable and continuous pulse outputs (signal and idler) in fs, with 108 Hz repetition rate and a miniwatt average power level. A KTP's OPO that are pumped by a 1064 nm Nd:YAG laser has generated as high as above 66% efficiency for degenerately converting to 2120 nm.






Fig.4 OPO pumped at 532 in X-Y plane

The novel developed application is the non-critical phase matched (NCPM) KTP's OPO/OPA. As shown in Fig.5, for pumping wavelength range from 0.7 µm to 1 µm, the output can cover from 1.04 µm to 1.45 µm (signal) and from 2.15 µm to 3.2 µm (idler). More than 45% conversion efficiency was obtained with narrow output bandwidth and good beam quality.




Fig.5 Type II NCPM OPO

Applications for E-O Devices

In addition to unique features, KTP also has promising E-O and dielectric properties that are comparable to LiNbO₃. These excellent properties make KTP extremely useful to various E-O devices. Table 1 is a comparison of KTP with other E-O modulator materials commonly used:

Phase Amplitude Materials 3 N R K N^7r^2/ϵ K $n^7 r^2 / \epsilon$ $(10-6/^{\circ}C)$ (pm/V) $(10-6/^{\circ}C)$ $(pm/V)^2$ (pm/V) $(pm/V)^2$ KTP 15.42 1.80 35.0 31 6130 27.0 11.7 3650 7410 42.0 LiNbO₃ 27.90 2.20 8.8 82 20.1 3500 KD*P 48.00 1.47 24.0 9 178 24.0 8.0 178 5.90 1.74 6.4 24 335 1.2 15.0 124 LiIO₃

Table 3. Electro-Optic Modulator Materials

From Table 1, clearly, KTP is expected to replace LiNbO₃ crystal in the considerable volume application of E-O modulators, when other merits of KTP are combined into account, such as high damage threshold, wide optical bandwidth (>15 GHZ), thermal and mechanical stability, and low loss, etc.

Applications for Optical Waveguides

Based on the ion-exchange process on KTP substrate, low loss optical waveguides developed for KTP have created novel applications in integrated optics. Table 2 gives a comparison of KTP with other optical waveguide materials. Recently, a type II SHG conversion efficiency of 20% /W/cm² was achieved by the balanced phase matching, in which the phase mismatch from one section was balanced against a phase mismatch in the opposite sign from the second. Furthermore, segmented KTP waveguide have been applied to the type I quasi-phase-matchable SHG of a tunable Ti:Sapphire laser in the range of 760-960 mm, and directly doubled diode lasers for the 400-430 nm outputs.

Materials r (pm/V) $\varepsilon_{\rm eff}(\varepsilon_{11}\varepsilon_{33})^{1/2}$ $n^3 r / \epsilon_{\rm eff} (pm/V)$ n KTP 35 1.86 13 17.30 LiNbO₃ 29 2.20 37 8.30 KNbO₃ 25 2.17 30 9.20 **BNN** 56 2.22 86 7.10 BN 56-1340 2.22 119-3400 5.1-0.14 GaAs 1.2 3.60 14 4.00 2.36 BaTiO₃ 28 373 1.00

Table 4. Electro-Optic Waveguide Materials

KTP's Parameters

Table 5. Specifications

Dimension Tolerance	$(W \pm 0.1 \text{ mm}) \times (H \pm 0.1 \text{ mm}) \times (L + 0.5/-0.1 \text{ mm}) \times (L \ge 2.5 \text{ mm})$ $(W \pm 0.1 \text{ mm}) \times (H \pm 0.1 \text{ mm}) \times (L + 0.1/-0.1 \text{ mm}) \times (L < 2.5 \text{ mm})$	
Clear Aperture	Central 90% of the diameter	
Internal Quality	No visible scattering paths or centers when inspected by a 50 mW green laser	
Surface Quality (Scratch/Dig)	10/5 to MIL-PRF-13830B	
Flatness	≦λ/8 @633 nm	
Transmitted Wavefront Distortion	≦λ/8 @633 nm	
Parallelism	20 arc sec	
Perpendicularity	≤ 15 arc min	
Angle Tolerance	≦0.25 °	
Chamfer	≦0.2 mm × 45 °	
Chip	≦0.1 mm	
Damage Threshold	>1 GW/cm ² @1064 nm, 10 ns, 10 Hz (AR-coated) >0.3 GW/cm ² @532 nm, 10 ns, 10 Hz (AR-coated)	
Quality Warranty Period	One year under proper use.	

AR-coatings

CASTECH provides the following AR-coatings:

- Dual Band AR-coating (DBAR) of KTP for SHG of 1064 nm; low reflectance (R<0.2% @1064 nm and R<0.5% @532 nm)
- High reflectivity coating: HR 1064 nm & HT 532 nm, R>99.8% @1064nm, T>90% @532 nm
- Broad Band AR-coating (BBAR) of KTP for OPO applications.
- High damage threshold (>300 MW/cm² at both wavelengths)
- Long durability
- · Other coatings are available upon request.